



# VALVE PACKING CONTROLLER-ONE EVO

## Composition

The Controller One Evo sealing ring kit consists of expanded mineral graphite Valvograph and GR80SGR braid. This set has been designed and manufactured to meet the growing demand for reliable products that comply with TA LUFT VDI 2440 Low Emission requirements. The graphite rings are stamped in the characteristic Cup & Cone section, which, when compressed, generates a thrust towards the stem and the chamber, improving the sealing level and meeting low emission requirements even with low clamping loads. Controller One Evolution is made with pure graphite to ensure moderate weight loss at high temperatures, in accordance with EN14772 - Section 6.7 requirements.


## Characteristics

This set of gaskets for industrial valves is designed for low emission applications with hydrocarbons, hydrogen, VOCs, VHAP, non-oxidizing chemicals, and steam. Its Cup & Cone configuration allows for maintaining a high seal even with reduced clamping loads. The pure graphite used offers superior resistance to high temperatures and operating loads, meeting the strictest requirements for industrial applications.

## Applications

Controller One Evolution is ideal as a stem sealing set for industrial valves in low emission applications. Thanks to its ability to maintain reliable sealing even in severe operating conditions and its chemical and thermal resistance properties, it is suitable for a wide range of industrial services, ensuring reliable performance and compliance with the highest safety and regulatory standards.

## Tech Data

	P bar	lbf/in <sup>2</sup>	Vm/S	f/pm	pH	T °C	T °F
	300	4500	1	200	0÷14	-200 ÷ 450 / 650	-325 ÷ 840 / 1200

- Never use the product to the maximum temperature and pressure associated. Consult the manufacturer for further information
- The peak temperature can be sustained for short exposures
- With weakly oxidizing agents and hot air the temperature must be limited to 450 °C
- With steam and non-oxidizing fluids the temperature must be limited to 650 °C
- Graphite and carbon cannot be used with oxidizing fluids



## Valve Packing Controller-One Evo

The range of graphite products for industrial valve stems offers a wide selection of models to ensure optimal choice in every situation. These gaskets are made from materials that meet rigorous industry standards, including ASTM F2168 and ASTM F2191, taking into account the main deviations provided for by IOGP standards and major oil and gas producers. The Carrara range ensures a level of certification suitable for every technical specification and sustainable application of graphite products.



The information in this publication, as well as any additional information provided to users, is based on experience and is shared to the best of our current knowledge. However, due to numerous factors beyond our knowledge and control that may affect the use of these products, no warranties are provided or implied regarding this information. The operating limits presented in this publication do not imply that these values can be applied simultaneously. Do not use the product at the maximum temperature and pressure values simultaneously. The maximum temperature is suitable only for short-term exposure under specific conditions. Specifications are subject to change without prior notice. The picture in the DS may not accurately depict the exact color and/or markings of the product.

 **CARRARA**  
GLOBAL SEALING SOLUTIONS

**Carrara S.p.A.**,  
Via Provinciale 1/E - 25030 Adro - BS - Italia  
tel. +39 030 7451121 / fax +39 030 7451130  
[www.carrara.it](http://www.carrara.it) - [info@carrara.it](mailto:info@carrara.it)