



# CONTROLLER ONE EVO PLANIGRAPH ESP

## Composition

**CONTROLLER ONE EVO PLANIGRAPH<sup>ESP</sup>** is a combined stem packing composed of expanded graphite rings **Planigraph<sup>ESP</sup>** and **GR8622<sup>ESP</sup>** braided graphite rings.

## Characteristics

**CONTROLLER ONE EVO PLANIGRAPH<sup>ESP</sup>** is manufactured with modified **Planigraph<sup>ESP</sup>** graphite made according to strict guidelines. Maintaining the packing weight is essential in order to meet standards and minimize fugitive emissions in the long term.


The excellent sealing capabilities of **CONTROLLER ONE EVO PLANIGRAPH<sup>ESP</sup>** and the reduced fugitive emissions are born from a completely brand-new approach. This material is characterized by a reduced coefficient of friction and low permeability, better than those achievable with the current technology using lubricants, without compromising the chemical integrity of the material.

**CONTROLLER ONE EVO PLANIGRAPH<sup>ESP</sup>** is a Low Emissions ISO 15848 BH C01/C02 approved graphite packing, providing a valid solution to reduce OEM stock seal types. It can be used for all Oil & Gas, Cyogenic, H<sub>2</sub> and most Chemical services, as well as steam.

## Applications

**CONTROLLER ONE EVO PLANIGRAPH<sup>ESP</sup>** is a graphite stem packing seal designed for low-emission services in industrial valves. It is suitable for use with hydrocarbons, cryogenic, hydrogen, VOCs, VHAPs, non-oxidizing chemical compounds, and steam. **CONTROLLER ONE EVO PLANIGRAPH<sup>ESP</sup>** is rated for up to 500 bar. It is designed to operate under all pressure conditions covered by classes 150 to 2500 lbs, thanks to its special wiper rings, GR8622<sup>ESP</sup> style (for extreme applications, such as those requiring API 5000 and API 10000 standards, please contact the Carrara Technical Department).

## Tech Data

	P bar	lbf/in2	Vm/S	f/pm	pH	T°C	T°F
	500	7500	1	200	0 ÷ 14	-200 ÷ 450 / 650	-320 ÷ 850 / 1200

- Never use the product to the maximum temperature and pressure associated. Consult the manufacturer for further information
- With weakly oxidizing agents and hot air the temperature must be limited to 450 °C
- With steam and non-oxidizing fluids the temperature must be limited to 650 °C
- Graphite and carbon cannot be used with oxidizing fluids



## CONTROLLER ONE EVO PLANIGRAPH ESP

### APPROVALS

- ISO 15848 BH-C01/C02-400°C (750°F)
- Limited detrimental materials and Ash
- Weight Loss API std 622 3rd Ed., EN 14772 S.6.7, FSA-G-604-07 METHOD B
- TQ39 - 50.000 h Target Temperature 408°C
- Fire Test API 607, API 6FA, ISO 10497
- Corrosion Test RT and HT
- MESC 85/203 and 85/204
- H2 Compatible
- PTFE Free
- PFAS Free
- Wet Lubricant Free



The information in this publication, as well as any additional information provided to users, is based on experience and is shared to the best of our current knowledge. However, due to numerous factors beyond our knowledge and control that may affect the use of these products, no warranties are provided or implied regarding this information. The operating limits presented in this publication do not imply that these values can be applied simultaneously. Do not use the product at the maximum temperature and pressure values simultaneously. The maximum temperature is suitable only for short-term exposure under specific conditions. Specifications are subject to change without prior notice. The picture in the DS may not accurately depict the exact color and/or markings of the product.



**Carrara S.p.A.**,  
Via Provinciale 1/E - 25030 Adro - BS - Italia  
tel. +39 030 7451121 / fax +39 030 7451130  
[www.carrara.it](http://www.carrara.it) - [info@carrara.it](mailto:info@carrara.it)