

CONTROLLER ONE EVO PLANIGRAPH ESP

Composition

CONTROLLER ONE EVO PLANIGRAPH^{ESP} is a combined stem packing composed of expanded graphite rings **Planigraph**^{ESP} and **GR8622**^{ESP} braided graphite rings.

Characteristics

CONTROLLER ONE EVO PLANIGRAPH is manufactured with modified Planigraph graphite made according to strict guidelines. Maintaining the packing weight is essential in order to meet standards and minimize fugitive emissions in the long term.

The excellent sealing capabilities of **CONTROLLER ONE EVO PLANIGRAPH**^{ESP} and the reduced fugitive emissions are born from a completely brand-new approach. This material is characterized by a reduced coefficient of friction and low permeability, better than those achievable with the current technology using lubricants, without compromising the chemical integrity of the material.

CONTROLLER ONE EVO PLANIGRAPH^{ESP} is a Low Emissions ISO 15848 BH C01/C02 approved graphite packing, providing a valid solution to reduce OEM stock seal types. It can be used for all Oil & Gas, Cyogenic, H₂ and most Chemical services, as well as steam.

Applications

CONTROLLER ONE EVO PLANIGRAPH^{ESP} is a graphite stem packing seal designed for low-emission services in industrial valves. It is suitable for use with hydrocarbons, cryogenic, hydrogen, VOCs, VHAPs, non-oxidizing chemical compounds, and steam. CONTROLLER ONE EVO PLANIGRAPH^{ESP} is rated for up to 500 bar. It is designed to operate under all pressure conditions covered by classes 150 to 2500 lbs, thanks to its special wiper rings, GR8622^{ESP} style (for extreme applications, such as those requiring API 5000 and API 10000 standards, please contact the Carrara Technical Department).

Tech Data

	P bar	lbf/in2	Vm/S	f/pm	рН	т∘с	T°F
基	500	7500	1	200	0 ÷ 14	-200 ÷ 450 / 650	-320 ÷ 850 / 1200

- Never use the product to the maximum temperature and pressure associated. Consult the manufacturer for further information
- With weakly oxidizing agents and hot air the temperature must be limited to 450 $^{\circ}$ C With steam and non-oxidizing fluids the temperature must be limited to 650 $^{\circ}$ C
- Graphite and carbon cannot be used with oxidizing fluids



CONTROLLER ONE EVO PLANIGRAPH ESP

APPROVALS

- ISO 15848 BH-C01/C02-400°C (750°F)
- Limited detrimental materials and Ash
- Weight Loss API std 622 3rd Ed., EN 14772 S.6.7, FSA-G-604-07 METHOD B
- TQ39 50.000 h Target Temperature 408°C
- Fire Test API 607, API 6FA, ISO 10497
- Corrosion Test RT and HT
- MESC 85/203 and 85/204
- H2 Compatible
- PTFE Free
- PFAS Free
- Wet Lubricant Free



